



# Internal CO<sub>2</sub> Sensor for Automotive Applications



## NDIR CO<sub>2</sub> Single Channel, Diffusion Sampling Method

The Telaire Internal Carbon Dioxide (CO<sub>2</sub>) Sensor is a nondispersive infrared (NDIR) CO<sub>2</sub> sensor that implements a single channel diffusion sampling method for automotive HVAC applications, including automatic fresh air control and safety sensing for CO<sub>2</sub> refrigerants.

Along with the patented ABC Logic™ lifetime calibration warranty, its low power consumption, compact design and simple product integration, make this an affordable gas sensing solution.

### Benefits

- Safety - Measure and control in-cabin CO<sub>2</sub> levels to prevent driver drowsiness.
- Energy Savings - Reduce variations in heating and cooling in-cabin through demand control ventilation.

### Applications

- Automotive HVAC - In-cabin air quality and comfort control.
- CO<sub>2</sub> refrigerant leak detection

### Features

- ABC Logic™ - Lifetime calibration warranty
- Lin 2.0 output
- Low power consumption
- Selectable power modes
- Mode-based sampling rate
- Compact design
- Wide temperature range

**Amphenol**  
Advanced Sensors

# Internal CO<sub>2</sub> Sensor Specifications

## General Performance:

### ABC Logic

This sensor implements an algorithm to self-calibrate to its ambient environment. The sensor uses readings during fresh air conditions to make the correction. ABC Logic corrects for a variety of use factors including transitions to new environments, change in altitudes, mishandling and aging of the sensor. Data for the algorithm is gathered during normal use of the sensor and corrections are implemented every 504 hours of continuous use.

### Accuracy and Measurement Range:

- 400 to 5,000 ppm CO<sub>2</sub>: +/-200 ppm
- 5,000 ppm to 4% CO<sub>2</sub>: +/- 10% of the reading
- 4% to 6.5%: accuracy not specified
- Temperature Dependence (outside 0C to 50C): +/- 0.5% of the reading

### Measurement and Sample Rate Characteristics:

- Active Mode: 5 seconds sample rate
- Low Power Mode: 15 seconds sample rate
- Sleep Mode: 5 minute sample rate
- Warm-up mode: 5 seconds after power up
- Warm-up time to full accuracy: 2 minutes

## Mechanical:

### Enclosure

- PBT GF15 Black

### Weight

- 5g

### Conformal Coating

- Electronic components are conformal coated.

## Environmental:

### Operating Temperature Range

- -40°C to + 90°C

### Storage Temperature Range

- -40°C to +110°C

### Relative Humidity

- 0-95% non-condensing

## Electrical Characteristics:

### Voltage Ratings

- Input Voltage: 9VDC - 16VDC
- LINbus Voltage: 9VDC - 40VDC


### Current Consumption

- Active Mode Current (average): 20mA
- Low Power Mode Current (average): 15mA
- Sleep Mode Current (no measurement): 25uA
- Peak Current (max): 120mA

# Internal CO<sub>2</sub> Sensor Specifications *(cont.)*

## Cable and Connector


### Connection

Mating Connector	TE AMP 4-1718346-1	
Socket Configuration		1 ~ Ground (Common)
		2 ~ LIN
PCB Pads		3 ~ Supply +V
		1 ~ Supply +V (Square pad)
		2 ~ LIN
		3 ~ Ground (Common)

## Available Models

Part No.	Sampling Method	Range	Feature
T6743-40KE	Diffusion	0-40,000 ppm	Sensor with Enclosure
T6743-40K	Diffusion	0-40,000 ppm	No Enclosure, PCBA only

### PIN LAYOUT



## LIN Interface

The sensor implements a LIN interface defined by a generic LDF file.

## LIN Output Signals

### Carbon Dioxide

CO<sub>2</sub> Concentration: 1 ppm Resolution

### Alarm Output

Limit-based threshold alarm signal with hysteresis.

### Error Response

Indicates when a node or frame error is detected.

### Diagnostics

Flag used to indicate a diagnostic issue to the host.

### Device Ready

Indicates when the sensor is ready to take a measurement.

# Amphenol

**Advanced Sensors**

[www.telaire.com](http://www.telaire.com)

[www.amphenol-sensors.com](http://www.amphenol-sensors.com)

© 2023 Amphenol Corporation. All Rights Reserved. Specifications are subject to change without notice.  
Other company names and product names used in this document are the registered trademarks or trademarks of their respective owners.